

## ルーペ

NL-5 / NL-10 / NL-15 / NL-22

この度は、ルーペをお買い上げ頂きまして、誠にありがとうございます。

ご使用に際し、本説明書を最後までお読みいただき、正しい使い方でお使いいただきますようお願い申し上げます。

## 焦点の合わせ方

被検物にルーペをあてて見るタイプで、置くだけで焦点が合います。

## ■仕様

品番	NL-5	NL-10	NL-15	NL-22
倍率	5倍	10倍	15倍	22倍
視野	34mm	22mm	12mm	3.5mm
有効径	25mm	24mm	18.5mm	12mm
レンズ材質	ガラス			
本体サイズ	約φ38×H67mm	約φ34×H42mm	約φ36×H33mm	約φ36×H24mm
質量	約25g	約25g	約18g	約12g
付属品	ウエス 1枚			

※外観、仕様などは製品改良のため、予告なしに変更することがありますのでご了承ください。

## ■ご使用にあたって

## ⚠ 警告

- ルーペを通して太陽やスポットライト、サーチライトなどの強い光を絶対に見ないでください。失明の恐れがあります。
- ルーペを通して太陽光や強い光を体に当てないでください。やけどの恐れがあります。
- ルーペを直射日光及び反射光の当たる場所に放置しないでください。発火の恐れがあります。

## ⚠ 注意

- 落としたりぶつけたりしないでください。
- 雨の中や湿気の多い場所、高温・低温環境下、直射日光の当たる場所での使用、保管はおやめください。
- レンズの表面の汚れは強くこするとレンズに傷をつける恐れがありますので、柔らかい布で軽く拭き取ってください。
- 本製品の用途以外のご使用は、事故やけがの原因になりますので、絶対におやめください。

**NSK** 新潟精機株式会社

〒955-0055 新潟県三条市塚野目5丁目3番14号  
 ☎ (0256)33-5502(代) FAX (0256)33-5528  
 URL <https://www.niigataseiki.co.jp>  
 I492-K1 2601

## LOUPE

NL-5 / NL-10 / NL-15 / NL-22

Thank you for purchasing the Loupe.  
Please read this manual thoroughly before use to insure proper operation and long service.

### FOCUSING

This type of Loupe is designed to be placed directly on surface being viewed.

### SPECIFICATIONS

Model No.	NL-5	NL-10	NL-15	NL-22
Magnification	5X	10X	15X	22X
Field of View	34mm	22mm	12mm	3.5mm
Effective Diameter	25mm	24mm	18.5mm	12mm
Material	Lens : Glass			
Dimensions	approx. $\phi 38 \times H67$ mm	approx. $\phi 34 \times H42$ mm	approx. $\phi 36 \times H33$ mm	approx. $\phi 36 \times H24$ mm
Weight	approx. 25g	approx. 25g	approx. 18g	approx. 12g
Accessories	Lens Cloth 1			

※The appearance and specifications are subject to change without notice for product improvement.

### PRODUCT NOTES

#### CAUTION

- Never look at sun or strong light through the Loupe, there is risk of eye damage.
- Do not expose skin to sunlight or strong light through the Loupe, there is risk of burns.
- Do not leave Loupe in direct or indirect sunlight, there is risk of fire.

#### NOTICE

- Handle with care. Please protect from strong forces or shock.
- Please do not use or store instrument in rain or locations with excessive humidity. Do not use or store at extreme high or low temperatures. Keep out of direct sunlight.
- Clean lens with lens cloth and use gentle motion to prevent dirt from scratching surface.
- Use only as directed; improper use may cause accident or injury.

**NSK Niigata Seiki Co., Ltd.**

5-3-14, Tsukanome, Sanjo, Niigata, Japan, 955-0055  
 Tel. : +81-256-33-5522 Fax. : +81-256-33-5518  
 MAIL intl.sales@niigataseiki.co.jp  
 URL https://www.niigataseiki.net/en/